

A-LINE MULTI-FUNCTION PATIENT & EXAM LUMINAIRE

PROJECT: _____
 TYPE: _____
 PRODUCT: _____
 APPROVED BY: _____

PRODUCT FEATURES

- Intended for Patient Rooms, Skilled Nursing Facilities, Convalescent Care, Hospice and more
- 4 Functional modes: Ambient, Exam, Reading, and Nightlight
Asymmetric distribution for Exam
- Recommended to be used in pairs adjacent to the patient bed. Sold individually. Must order a "left" and a "right" for a complete pair.
- Fixture is certified to UL standards, IP64 rated per IEC60598, and NSF2 Splash Zone/Non-Food Zone listed, CCEA approved
- This product is Made in America and complies with Buy American Act (BAA) requirements and the Build America BuyAmerica Act (BABAA)



CCAL

ORDERING INFORMATION

Example: CCAL4L-G-AE30-RD30-90C-AM-UN-DM1



CCAL 4						
Series	Nominal Size* 4 = 4'	Position L = Left R = Right	Mounting G = 9/16" and 15/16" Lay-In Grid FL = Drywall Flange	Ambient & Exam Lumen Output (individual) AE = Nominal 2300lm Ambient/5800lm Exam CL = Custom Lumens*	Ambient & Exam Color Temp.* 30 = 3000K 35 = 3500K 40 = 4000K Tunable White** TW1 = 2700K to 5000K TW2 = 2700K to 6500K *Selected CCT will be the same for both ambient and exam functions. **Must specify Tunable White Driver.	Reading (Optional)* RD30 = Reading light 3000K RD35 = Reading light 3500K RD40 = Reading light 4000K *Reading lights in both fixtures. When Reading is selected a 3rd circuit is standard. Reading light CCT can differ from color temp selected for ambient and exam functions.
	*Consult factory for other lengths.	*Recommended to be used in pairs adjacent to the patient bed. Will need to order both a Left & a Right for a complete pair.		*Must be specified at time of quote. Must not exceed fixture maximum output.		

90C			
CRI	Voltage	Driver Type	Options
90C = 90 CRI	12 = 120V 27 = 270V 34 = 347V UN = Universal (120-277V)	DM1 = 0-10V Dimming with 1-100% range DMT = 0-10V & TRIAC/ELV Tunable White Driver* TWD = 2-Channel DALI Type 8 with 1-100% range TWO = 2-Channel 0-10v with 1-100% range *Tunable White Driver requires choice of TW1 or TW2 in Color Temp column.	EL1 = Emergency Battery (10W) LV06 = Low Voltage Controller* LNA = Amber Nightlight (585-595nm)** AM = Antimicrobial white C = Custom (RAL number required) *N/A with emergency battery. **When specified in pairs, Nightlight will be in Right unit.

A-LINE MULTI-FUNCTION PATIENT & EXAM LUMINAIRE

SPECIFICATIONS

HOUSING: Extruded aluminum construction with aluminum endcaps. Closed cell neoprene pad gasket on inside flange.

LENS: .125" acrylic lens with symmetric / asymmetric distribution.

LED: Available in three color temperatures 3000K, 3500K and 4000K with maximum 3-step MacAdam variation allowance. Tunable White also available, from 2700K – 5000K or 2700K – 6500K. Minimum 50,000 hours with 70% lumen maintenance in a 25°C ambient temperature, compliant with IES LM-80 testing standards.

ELECTRICAL: 120-277VAC or 347VAC, 50/60Hz electrical input. High power factor electronic, constant current driver (<20% THD, >0.90 PF). Standard 0-10V dimming with 1-100% range for Ambient and Reading loads. Ambient and Exam compartments default to 2 circuits (1 Ambient, 1 Exam) unless otherwise specified. When Reading is selected, Reading is supplied on an additional independent circuit.

TUNABLE DRIVER OPTIONS:

TWO = 2 CHANNEL 0-10V one channel for brightness, one channel for CCT

TWD = 2 CHANNEL DALI8 one channel for brightness, one channel for CCT

LOW VOLTAGE CONTROL: LV06 specifies the Curbell LVC2000-06 low voltage controller. Standard configuration provides three low voltage control circuits per pair: LV circuit 1 controls Ambient as dimming, LV circuit 2 controls Reading as dimming, and LV circuit 3 triggers Exam mode and drives the Ambient and Exam functions to full brightness to provide the complete exam function. Night Light, when ordered, is wired as a separate line voltage circuit and is not controlled through LV06. One controller per pair is provided. Compatible with normally-open momentary dry contacts from pillow speakers, bedside rails, or wall switches. Other configurations are available – consult factory. Leads are factory labeled for field installation. Controls and any additional accessories by others.


FINISH: White polyester powder coat finish following multi-stage iron phosphate pretreatment. Optional antimicrobial finish for all room side exposed surfaces available. Custom finishes also available.

INSTALLATION: Recessed Grid (9/16" or 15/16") or Flange.

WARRANTY: Five (5) year warranty.

LABEL: Fixture is certified to UL standards by Intertek Testing Laboratory. IP64 rated per IEC60598. Certified for NSF2 Splash Zone / Non-Food Zones.

DIMENSIONAL DATA



New Star Lighting

2225 W Pershing Rd, Chicago, IL 60609
(773) 847-1400
www.newstarlighting.com

Specifications and dimensions are subject to change without notice. For additional options and dimensional details, please consult your New Star Lighting representative.

© 2026, New Star Lighting. All rights reserved. Unauthorized duplication or distribution is prohibited.

A-LINE MULTI-FUNCTION PATIENT & EXAM LUMINAIRE




PERFORMANCE DATA

Performance at 3500K @ 90CRI. If 80CRI is specified, there is a 10-15% increase in delivered lumens. Consult factory. Data is based on a pair of 4 foot luminaires using one driver each.

MODEL	FUNCTION	CCT	LUMENS DELIVERED	EFFICACY (lm/w)	INPUT POWER (w)
CCAL	Ambient	30K	4533	91	50
		35K	4736	95	50
		40K	4861	97	50
	Exam + Ambient	30K	11278	91	124
		35K	11782	93	124
		40K	12092	97	124
	Reading	30K	2325	93	25
		35K	2375	95	25
		40K	2425	97	25
	Nightlight	18K	138	23	6

*When luminaires are in exam mode the ambient will also be on. These values represent the combined lumen package of both ambient and exam.


PHOTOMETRIC CURVES



	AMBIENT	EXAM	READING	NIGHTLIGHT
A-Line	'15X'15 ROOM	ON BED	ON BED, IN READING	3' SURROUNDING
Avg. FC	19	100	24	1.1
Avg. to Min	2.71	1.7	1.74	2.85

A-LINE MULTI-FUNCTION PATIENT & EXAM LUMINAIRE

LOW VOLTAGE CONTROLLER · CURBELL LVC2000-06



- 0-10V dimming
- Universal 120-277VAC input voltage
- Controls up to three loads
- Standard LV06 configuration: two dimming loads and one on/off exam trigger load
- Exam function raises multiple loads to maximum light with the touch of a button
- Step dimming levels: 100%, 75%, 50%, 25%, Off
- Smooth dimming: press and hold to decrease or increase output
- Bedside interface is low-voltage Class 2 (30VDC @ 1A or less)

Note: Night Light, when ordered, is wired as a separate line-voltage circuit and is not controlled through LV06. One controller is provided per fixture pair. Other configurations are available – consult factory.

Operating Parameters

Model / Option Code	Curbell LVC2000-06 / LV06
Input Voltage	Universal 120-277VAC input voltage
Dimming Type	0-10V dimming
Supported Loads	Controls up to three loads
Standard LV06 Wiring	
Exam Function	Single control input drives multiple loads to maximum lighting levels
Switch Requirements	Normally-open momentary dry contacts
Compatible Controls	Pillow speaker, bedside rail, and/or wall switch
Step Dimming	100%, 75%, 50%, 25%, Off
Smooth Dimming	Press and hold to decrease or increase light level once load is on
Bedside Safety	Low-voltage Class 2 at bedside (30VDC @ 1A or less)



New Star Lighting

2225 W Pershing Rd, Chicago, IL 60609
(773) 847-1400
www.newstarlighting.com

Specifications and dimensions are subject to change without notice. For additional options and dimensional details, please consult your New Star Lighting representative.

© 2026, New Star Lighting. All rights reserved. Unauthorized duplication or distribution is prohibited.